



---

Cartridge Pre-heat Box 796993

Caution: For DGX products use only switch position 1.

- Can be used with up to 6 cartridges, depending on the product and or foil packs.
- Thermostat maintains constant temperature to prevent over heating.
  - Switch position 1 (60° C) suitable for DGX products.
  - Switch position 2 (90° C) for warming of PE cartridges (e.g. Terokal 5055).
- Pre-heat Terostat 8599 HMLC for about 30 minutes on position 1.
- Pre-heat Terostat 8630 2C HMLC for about 60 minutes on position 1.
- Terostat 8599 HMLC / 8630 2C HMLC can be pre-heated several times for long periods without suffering any loss of quality.
- For Henkel Loctite 7255, use position 1 for 30 minutes.

Technical details:

Case outer dimensions	400 x 300 x 140 mm
Weight	2.9 g
Voltage	220 V
Watts	200 Watts

Note:

If using the unit in the US, use a power adapter on the European power plug, or cut-off the connector and install a 220 VAC connector that suits your facility.